

# ***USERS'MANUAL***



**Specially For Camera Lens Adjustment**

Dear customers, thanks for using this product, and wish it can bring you the convenience, before start to use this product, please read the following items carefully.

1) Forbidden to use under high temperature, especially not allowed to use in high Humidity bath room, the most suitable working temperature is approximate -20°C-60°C.

2) Keeping it away from water and other liquid when using this product, otherwise there may be danger such as shock and fire-arise happen! In order to keep your safety, please use the adapter supplied (Regarding the damages caused by using adapters from other supplier, we are not responsible to it).

3) Don't set the machine in the place of bared sunshine.

4) Please place the machine in the place where the children can not reach, in order to keep it away from damage by dropping or bumping at sharp object.

5) Do not charge the battery with the damaged charger.

6) Do not charge the battery longer than the prescribed time.

7) When start to charge the battery for the first time, or start to use the battery again several months later, please charge it fully.

8) Charge the battery fully, and run out of the power completely, and then charge it again in order to make its lifespan longer. It will shorten the battery's lifespan when charging it immediately after using for a short time,

9) Over charge or discharge will shorten the battery's lifespan.

10) When the battery's working time is apparently shorter than new one, please change the battery.

11) The battery is consumption product, so its working time will shorten as time goes by.

12) Be careful to keep the connection of DC convertor or battery away from any conductor (such bracelet, necklace and so on) in order to avoid short circuit, otherwise it may cause fire disaster.

13) Do not dismantle the machine yourself, if any question, please contact our wholesaler or company.

#### 1、Profile

It's a 2.5" LCD monitor, PAL/NTSC are both available in this machine. It adopts LED as the back lamp, low consumption, low interference, adopt the IC to realize power management, and with the feature of stablbing the current of back lamp.

#### 2、Main parameter

Product name: 2.5" LCD monitor

Sign of system: PAL/NTSC

Resolution: 480\*234

View angle: ( up/down/left/right): (10/30/40/40)

Brightness: 200cd/m<sup>2</sup>

Video input: 1.0Vp-p 75ohm

Power input: DC 5V

Rating power consumption:1.2W

Battery:3.7V 1000mA( Nokia N73 is available)

Working temperature:0-60°C


Store temperature: -30~60°C

Environment relative humidity: 5-95%RH

Externality dimension: L 85\*H 64\*P 21mm

Weight (stand-alone):90g

#### 3、Basic operation



No.	Description
1	BRIGHTNESS
2	COLOR
3	POWER-ON/OFF
4	AV INPUT
5	DC 5V
6	LED INDICATION
7	BATTERY SLOT

#### 4、Accessories

Use's manual	1pc;	charger	1pc
Battery	1pc ;	AV cable	1pc
Bracket	1pc ;	Wrist strap	1pc